





Interior MRI



Yoke - Wall





Yoke - Ceiling





Hub - Wall





Hub - Ceiling





Horizontal Stem





Cantilever Arm



CM Kit



Pier



Specifications:

- **Extruded** - Extruded .125" aluminum housing.
- **Solid** - Roll-formed .05" aluminum housing.
- **Perforated** - Roll-formed .05" perforated aluminum housing.
- Cast aluminum end caps. Aluminum mounting brackets.
- Housing is field adjustable for application specific aiming and can be mechanically locked in the desired position.
- Hub and Horizontal Stem mountings utilize cast aluminum canopies. Horizontal Stem mount units include 1 1/2" stainless steel stems and square canopies. Hub mount supplied with round canopies.
- Yoke bracket is die-formed 14 gauge stainless steel.
- Cantilever arm mounting utilizes a yoke bracket with a 1 1/2" stainless steel stem and square canopy.
- Formed aluminum cover to fit over standard 4" junction box.
- The Ceiling Mount Kit utilizes a yoke bracket with a cover plate that mounts directly to a standard 4" junction box. Allows for 356° horizontal adjustability.
- Stainless steel exterior fasteners.
- Tungsten Halogen luminaires utilize a segmented, 95% reflective, specular clear, aluminum reflector. Impact and heat-resistant, tempered glass lens.
- Housing, endcaps, brackets, cover plates and stems painted to match. Standard finish is thermoset polyester powder coat. All metal surfaces go through a 5-stage pretreatment process prior to powder coat application.
- UL listed (US and Canada) for damp locations. (Not for exterior use).

Assistance Available: Please see our website, or call 262-242-1420 for more specific product information, applications assistance or modification requests.

FT	PW	VG	Lamp Wattage Range	Lamp
				FL
				MH
			150-250W	TH

SELECT STYLE

SELECT LAMPING

SELECT OPTICAL PACKAGE

SELECT VOLTAGE

SELECT FINISH

SELECT OPTIONS

WALL MOUNT

	Mounting	Housing
EIW 2130	Yoke	Extruded
EIW 2132	Yoke	Perforated
EIW 2134	Yoke	Solid
EIW 2136	Hub	Extruded
EIW 2138	Hub	Perforated
EIW 2140	Hub	Solid
EIW 2142	Horiz. Stem	Extruded
EIW 2144	Horiz. Stem	Perforated
EIW 2146	Horiz. Stem	Solid
EIW 2148	Cant. Arm	Extruded
EIW 2150	Cant. Arm	Perforated
EIW 2152	Cant. Arm	Solid

Lamping Detail	
1T150	(1) 150W T4 DC BAY QTZ
1T250	(1) 250W T4 DC BAY QTZ

FT	Forward Throw
PW	Plane Wash
VG	Vertical Graze

120

PT_ Painted. (Include Paint Number)
See SPI Finish Selection Guide on pages 168-169.

CS Cut-off Shield.
For further details on Options, see Technical Notes on page 165.

CEILING MOUNT

	Mounting	Housing
EIC 2120	Yoke	Extruded
EIC 2122	Yoke	Perforated
EIC 2124	Yoke	Solid
EIC 2126	Hub	Extruded
EIC 2128	Hub	Perforated
EIC 2130	Hub	Solid
EIC 2132	CM Kit	Extruded
EIC 2134	CM Kit	Perforated
EIC 2136	CM Kit	Solid

Lamping Detail	
1T150	(1) 150W T4 DC BAY QTZ
1T250	(1) 250W T4 DC BAY QTZ

FT	Forward Throw
PW	Plane Wash

PIER MOUNT

	Mounting	Housing
EIM 2090	Pier	Extruded
EIM 2092	Pier	Perforated
EIM 2094	Pier	Solid

Lamping Detail	
1T150	(1) 150W T4 DC BAY QTZ
1T250	(1) 250W T4 DC BAY QTZ

FT	Forward Throw
PW	Plane Wash
VG	Vertical Graze

For additional lamping details and options, see Technical Notes on pages 160-161.

Reflections
Wall
Ceiling
Pendant

3.5
Wall
Ceiling
Pendant

5.0
Wall
Ceiling
Pendant
Pier
Cove
MRI
Shapes

6.0
Wall
Ceiling
Pendant
Pier
Cove
MRI

9.0
Wall
Ceiling
Pendant
Pier
Cove
MRI
Shapes

16.5
Wall
Pier
Pendant

Exterior

Lightruss