

Planning Guide

ExcelevatorElevators





We are a proud member of the Accessibility Equipment Manufacturers Association. This symbol assures you of our commitment to high quality and accessibility to everyone.



Waupaca Elevator Mission Statement

Our company's mission is to supply and service products that meet or exceed our customers' expectations of high quality, value, delivery and longevity. Our success is a direct reflection of our employees' involvement and commitment to excellence. We strive to continuously improve our products to ensure meeting the future requirements of our customers and facilitate competitive growth.



S P E C WIZARD

CSI 3-Part Specifications

Customize and download CSI 3-Part Specifications by logging on to:

<u>www.arcat.com</u> - specify Waupaca Elevator as the requested manufacturer <u>www.waupacaelevator.com</u> - go to "Architect Section" click on linking icon

SpecWizard is a faster easier way to customize CSI 3-part residential elevator specifications. Follow the above website information and choose the Spec Wizard icon. The drop down menus couldn't be any easier to use, just click on your choice of listed options and within a couple of minutes you have a completely customized spec.

Table of Contents

Introduction	4
Minimum - Maximum Dimensions	6
Car Opening Configurations	6
Hoistway Layout	7-9
Hoistway Illustration	10
Hoistway Specifications	11
Elevation and Hoistway Ceiling Height	12
Rail Layout and Jack Calculation	12
Controller/Electrical Space	13
Elevator Equipment	14
Elevator Series 014 Illustration	15



Introduction

This Planning Reference Guide is to be used as a guide to determine parameters of installation and steps taken to achieve a proper elevator installation. This guide may be used by the architect, contractor, dealer or home owner. The information in this guide is intended as an overview, each installation will have job specific specifications that must be followed. Do not attempt to construct a hoistway on this information alone.

Elevator installation is to be done by an authorized elevator contractor, and in accordance with installation instructions provided by the manufacturer. Installation must also be in compliance with requirements of the National Electric Code, American Society of Mechanical Engineers safety code, and state and local building codes. Waupaca Elevator's products are designed to meet the requirements of ASME - 17.1 National Elevator Codes for residential elevators and are fully certified by a registered professional engineer. Waupaca Elevator Company, Inc. elevators manufactured and installed under the proper parameters are warranted for 2 years. Manufacturer assumes no liability for equipment not installed in compliance with these codes.

Planning Steps

- 1. Locate local dealer and together determine the following:
 - A Select drive system, car type and design specifications
 - B Address national, state and local code requirements
 - C Hoistway size
 - D Car size, layout and options
 - E Machine room location and layout
 - F Electrical requirements
- 2. Obtain and follow site specific field drawings while building hoistway, doorways and any other construction related to the elevator.
- 3. Coordinate with dealer to install elevator.



Excelevator Mydraulic Elevator


Series **014**

Advantages

- Reliable
- Quiet Operation
- Smooth Ride
- Emergency Battery Descent

Hoistway Layout - Excelevator

Minimum and Maximum Dimensions





* Single Opening - 43 - 3/4"
 O.D. (outside dimension)
 minimum (rail is not centered in hoistway)

NOTE:


- 1) Minimum **D A** dimensions reflect rail centered in hoistway
- 2) Minimum **D A** dimension for car without a gate recess is 37" O.D. (outside dimension)
- 3) Car I.D. (inside dimensions) can not exceed 12 sq. ft. for 750 lb. Car I.D. (inside dimensions) can not exceed 15 sq. ft. for 950 lb.

Car Opening Configurations and Coding





- 1- The D A is the side on which the rail is attached.
- 2 The first letter refers to the attachment location of the gate.
- 3 The second letter refers to the location of the strike plate.
- 4 If present, the third letter "R" denote a recessed gate.





Hoistway Layout - Excelevator™

Construction Notes:

- Use specified rail backing from architect to frame into wall.
- The hoistway illustrations below show finished dimensions. Finished hoistway dimensions include drywall, plaster and paint.
- A maximum of 3" (see "f" below) are allowed between the closed hoistway door and the outer edge of the landing sill.
- Determine height of hall station by local code.
- Rough frame door in place with an extra inch of space on each side of the door to allow for door installation.

The following examples are of 750 lbs. and 950 lbs. units. Elevators are illustrated with accordion gates. The following layouts were designed for travel less than 25 feet, for distances up to 50 feet contact Waupaca Elevator Co.

These symbols are listed beside the car size Waupaca Elevator believes to be best suited for use by wheelchair passengers and their accompanying attendant.




Recommended size for wheelchair passenger



Recommended size for both wheelchair and attendant passengers


The following examples are of a T601 Sling. 750 lbs. -12 ft. sq. maximum & 950 lbs. -15 ft. sq. maximum




ELEVATOR		EXCELE	VATOR	ELEV	ATOR H	IOISTV	/AY D	IME	ENSI	ONS		
	HOISTWAY		FINISHED HOISTWAY DIMENSIONS									
LAY	OUT	CAR SIZE	а	b	С	d	е	f	g	h	i	
CODE 1	DCR	48" x 36"	51.75"	54.5"	27.25"	10.25"	36"	3"	48"	36"	27.5"	
LEFT SAME	DCR	も 54" x 40"	55.75"	60.5"	30.25"	14.25"	36"	3"	54"	40"	27.5"	
SIDE OPENING	DCR	他 60" x 36"	51.75"	66.5"	33.25"	10.25"	36"	3"	60"	36"	27.5"	
CODE 1	CDR	48" x 36"	52.75"	54.5"	27.25"	10.25	36"	3"	48"	36"	27.5"	
LEFT SAME SIDE OPENING	CDR	5 4" x 40"	55.25"	60.5"	30.25"	10.25	36"	3"	54"	40"	27.5"	
	CDR	慎 60" x 36"	52.75"	66.5"	33.25"	10.25	36"	3"	60"	36"	27.5"	




Hoistway Layout - Excelevator™




ELEVATOR			EXCELEVATOR ELEVATOR HOISTWAY DIMENSIONS												
HOIST					FINISHED HOISTWAY DIMENSIONS										
LAY	OUT	C	AR SIZE	а	b	С	d	е	f	g	h	i			
CODE 2	ABR		48" x 36"	51.75"	54.5"	27.25"	10.25"	36"	3"	48"	36"	27.5"			
RIGHT SAME	ABR	F	54" x 40"	55.75"	60.5"	30.25"	14.25"	36"	3"	54"	40"	27.5"			
SIDE OPENING	ABR	İŁ	60" x 36"	51.75"	66.5"	33.25"	10.25"	36"	3"	60"	36"	27.5"			
CODE 2	BAR		48" x 36"	52.75"	54.5"	27.25"	10.25"	36"	3"	48"	36"	27.5"			
RIGHT SAME SIDE OPENING	BAR	F	54" x 40"	55.75"	60.5"	30.25"	10.25"	36"	3"	54"	40"	27.5"			
	BAR	İŁ	60" x 36"	52.75"	66.5"	33.25"	10.25"	36"	3"	60"	36"	27.5"			






ELEVATOR HOISTWAY			EXCELE	VATOR	ELEVA	ATOR H	IOIST\	VAY I	DIME	ENSI	ONS	
			AR SIZE	FINISHED HOISTWAY DIMENSIONS								
LAY	OUT	C.	AR SIZE	а	b	С	d	е	f	g	h	i
CODE 3	ВС		48" x 36"	49.75"	56.5"	29.5"	15"	36"	3"	48"	36"	27.5"
LEFT	ВС	F	54" x 40"	53.75"	62.5"	32.5"	21"	36"	3"	54"	40"	27.5"
FRONT OPENING	ВС	İŁ	60" x 36"	49.75"	68.5"	35.5"	27"	36"	3"	60"	36"	27.5"
CODE 3	СВ		48" x 36"	49.75"	56.5"	29.5"	15"	36"	3"	48"	36"	27.5"
RIGHT FRONT OPENING	СВ	Ė	54" x 40"	53.75"	62.5"	32.5"	21"	36"	3"	54"	40"	27.5"
	СВ	İŁ	60" x 36"	49.75"	68.5"	35.5"	27"	36"	3"	60"	36"	27.5"


Hoistway Layout - Excelevator™





ELEVATOR		EXCELEVATOR ELEVATOR HOISTWAY DIMENSIONS												
HOIS			4 D 017 E	FINISHED HOISTWAY DIMENSIONS										
LAY	OUT	C.	AR SIZE	а	b	С	d	е	f	g	h	i		
CODE 4	ABR-DCR		48" x 36"	51.75"	55"	27.5"	10.25"	36"	3"	48"	36"	27.5"		
OPPOSITE	ABR-DCR	Ŗ	54" x 40"	55.75"	61"	30.5"	14.25"	36"	3"	54"	40"	27.5"		
OPENING	ABR-DCR	İŁ	60" x 36"	51.75"	67"	33.5"	10.25"	36"	3"	60"	36"	27.5"		
CODE 4	BAR-CDR		48" x 36"	52.75"	55"	27.5"	10.25"	36"	3"	48"	36"	27.5"		
OPPOSITE OPENING	BAR-CDR	F	54" x 40"	55.25"	61"	30.5"	10.25"	36"	3"	54"	40"	27.5"		
	BAR-CDR	İŁ	60" x 36"	52.75"	67"	33.5"	10.25"	36"	3"	60"	36"	27.5"		


ABR BC RIGHT ADJACENT 90° OPENINGS



DCR CB


LEFT ADJACENT 90° OPENINGS

CODE 6



ELEVATOR EXCE			ELEVATOR ELEVATOR HOISTWAY DIMENSIONS												
	HOISTWAY				FINISHED HOISTWAY DIMENSIONS										
LAY	OUT	CA	R SIZE	а	b	С	d	е	f	g	h	i	j	k	
CODE 5	ABR-BC		48" x 36"	49.75"	56.5"	27.25"	10"	32"	3"	48"	36"	36"	15.5"	27.5"	
RIGHT ADJACENT	ABR-BC	F	54" x 40"	53.75"	62.5"	30.25"	10"	36"	3"	54"	40"	36"	21.5"	27.5"	
90° OPENING	ABR-BC	İŁ	60" x 36"	49.75"	68.5"	33.25"	10"	32"	3"	60"	36"	36"	27.5"	27.5"	
CODE 6	DCR-CB		48" x 36"	49.75"	56.5"	27.25"	10"	32"	3"	48"	36"	36"	15.5"	27.5"	
LEFT ADJACENT	DCR-CB	F :	54" x 40"	53.75"	62.5"	30.25"	10"	36"	3"	54"	40"	36"	21.5"	27.5"	
90° OPENING	DCR-CB	İŁ	60" x 36"	49.75"	68.5"	33.25"	10"	32"	3"	60"	36"	36"	27.5"	27.5"	

Hoistway Illustrations - Excelevator™



Hoistway Specifications - Excelevator™

Refer to Illustration on previous page

ATTENTION CONSTRUCTION CONTRACTOR:

This is an example of a hoistway. Job specific documentation will be provided by Waupaca Elevator from which to construct the hoistway.

Hoistway Construction Requirements

(to be completed prior to elevator installation by contractor)

- 1. Electrical Requirements:
 - Dedicated 208/230 Volts, 30 AMP Single Phase, 60 Hertz.
 - A fused disconnect switch with branch 3 pole circuit wire to suit a 30 AMP service, fused for 20 AMP dual element (time delay fuse) with neutral.
 - 115 Volt, 15 AMP single phase circuit for car lighting.
 - Electrical wiring to comply with applicable codes.
- Unfinished/Un-installed Door Installation company may prefer a minimum of one
 hoistway door and associated framing be left unfinished/un-installed to accommodate
 elevator installation equipment and to prevent accidental damage to door and framing
 (preferably at grade level).
- 3. **Plumb and Square Hoistway** Hoistway must be plumb within 1/8 inch per 10 ft. of height and square at any point within 1/4 inch based on difference in diagonal measurements.
- 4. **Supportive Structure** Structure must be capable of supporting the appropriate loads. (see page 14)
- 5. **Machine Room** Machine room must be provided for operating equipment that meets national electric code clear space requirements and all local codes. Machine room must have a light switch and a convenience outlet. Temperature in machine room to be maintained between 60-110 ° F and relative humidity should not exceed 95%.
 - Access hole must be provided to route hydraulic hose or pipe (3/4" schedule 80) to hoistway.
- 6. **Telephone Connection** Code requires a telephone connection to the elevator car therefore, a phone line must be installed in the machine room.
- 7. **ASME 17.1 Sec 5.3** Hoistway to be constructed in accordance with ASME 17.1 Sec 5.3 and all local codes.
- 8. **Hoistway Door Security (Interlocks)** All hoistway doors require interlocks as well as a door handle and a latch set. Interlocks will be installed by the elevator installers. Waupaca Elevator recommends the use of solid core doors.
- 9. **No Alterations** Any alterations to the equipment without written authorization by Waupaca Elevator will void all warranties.
- 10. Pit Floor Strength Load on pit floor is 4,750 lbs. (minimum pit depth of 8").




Hoistway Ceiling Heights, Elevation and Rail Layout


Minimum Hoistway Ceiling Heights*

Inside Cab Dimension	6′ 10″	7′0″	7′ 4″	8′0″
Minimum Hoistway Ceiling Height	7′ 10″	8′0″	8′ 4″	9′0″

* Custom sized cabs will alter these dimensions. Waupaca Elevator will provide you with the appropriate dimensions. Please contact your local dealer to acquire alternate layouts.


This is a graphical representation of Waupaca Elevator's Excelevator which offers a total of six stops and a total travel distance of 50 feet.






Machine Room - Excelevator™

Typical Machine Room Layout



- 1. The Controller requires minimum clear space of 36" x 30" located directly in front of the controller (refer to illustration).
- A lockable service disconnect must be placed within sight of the controller and must be easily accessible from the latch side of the doorway.
- 3. A machine room or enclosure must be provided that meets national electrical code clear space requirements and all local codes. The machine room must contain a convenience outlet and light with switch. Temperatures in the machine room must be maintained between 60° 110°F (with a relative humidity not to exceed 95%).



Elevator Equipment - Excelevator™

Typical

Pump Unit

Valve


- Slack Rope Safeties
- Stopping Devices
- Interlocks
- Rail Segment

PUMP UNIT

HAS A CONSTANT DISPLACEMENT ROTARY SCREW PUMP POWERED BY A 2 1/2 / 3 1/2 HORSEPOWER, 208/230 SINGLE PHASE MOTOR. OIL TANK REQUIRES APPROXIMATELY 30 GALLONS OF AW-32 HIGH GRADE HYDRAULIC OIL. MACHINE ROOM CAN BE LOCATED UP TO 40' AWAY, REQUIRES PIPING IN SOME AREAS.


VALVE

TWO SPEEDS FOR SMOOTH STARTS AND STOPS. WORKING PRESSURE BETWEEN 250 & 750 PSI AT 5.5 GPM.




STOPPING DEVICES

MAGNETIC TAPE READER FOR LEVELING ACCURACY & TOP FINAL LIMIT SWITCH.




8 LBS. PER FOOT COMERCIAL ELEVATOR RAIL



SLACK ROPE SAFETIES

TWIN INSTANTANEOUS SAFETIES



Excelevator™ Elevator Series 014

