




# Vinyl Coated Grab Bars



- Choose from a variety of grab bar styles including straight, angled, corner, L-shaped, vertical, and safety supports
- Superior non-slip surface helps obtain a firmer grip
- Offers a secure and safe installation by giving the installer the flexibility to choose from up to 11 mounting holes on the mounting flange
- Most grab bars are ADA Compliant
- Available in white or ivory; other colors and grab bar styles available upon request



IPC.572/Rev.3

Inprocorp.com • 800.222.5556 • 262.679.9010  
World Headquarters S80 W18766 Apollo Drive, Muskego, WI 53150 USA

**ENDURANT®**  
WASHROOM SYSTEMS  
A DIVISION OF INPRO®

# Vinyl Coated Grab Bars

## Suggested Specifications

### PART 1 GENERAL

#### 1.01 SUMMARY

A. Grab bars safety and decoration.

#### 1.02 SECTION INCLUDES

A. Section 10800 – Color grab bars

#### 1.03 REFERENCES

A. American with Disabilities Act Accessibility Guidelines (ADAAG)

B. American National Standards Institute (ANSI)

C. American Society for Testing and Materials (ASTM)

#### 1.04 SUBMITTALS

A. Product Data: Manufacturer's standard product data for each product specified, including detail dimensions, function, and finish.

B. Samples: Manufacturer's color selection and verification samples – 6-1/2" in length.

C. Manufacturer's printed installation instruction: Include anchoring and fastening details.

#### 1.05 DELIVERY, STORAGE AND HANDLING

A. Deliver materials in unopened factory packaging to the jobsite

B. Inspect materials at delivery to assure that specified products have been received.

C. Store in original packaging in a climate controlled location away from direct sunlight.

#### 1.06 PROJECT CONDITIONS

A. Environmental Requirements: Products must be installed in an interior climate controlled environment.

#### 1.07 WARRANTY

A. Limited Lifetime Warranty against material and manufacturing defects.

### PART 2 PRODUCTS

#### 2.01 MANUFACTURER

A. Acceptable Distributor/Manufacturer:

Inpro® Corporation,

PO Box 406, Muskego, WI 53150, USA;

Telephone: 800-222-5556, Fax: 888-715-8407,

www.inprocorp.com

B. Substitutions: Not permitted.

C. Provide all grab bars and bathroom accessories from a single manufacturer.

#### 2.02 MANUFACTURED UNITS

A. Color grab bars.

1. Comply with ADA guidelines to withstand 300lbs of loading.

2. Corrosion resistant steel core with PVC finish coating, round 1 1/4" (32mm) diameter with 1 1/2" clear space to wall. Stainless steel flange.

3. Flange cover shall be snap-on design polyamide with no set screw. Flange cover to be 3 1/4" in diameter 1/8" thick.

4. Colors as selected from manufacturers standard range.

5. Straight bars length.

a. DSGBVST12, 12" long.

b. DSGBVST16, 16" long.

c. DSGBVST18, 18" long.

d. DSGBVST24, 24" long.

e. DSGBVST30, 30" long.

f. DSGBVST32, 32" long.

g. DSGBVST36, 36" long.

h. DSGBVST42, 42" long.

i. DSGBVST48, 48" long.

6. Corner safety support (reversible, horizontal)

a. DSGBVC2426, 24" by 26".

b. DSGBVC2436, 24" by 36".

c. DSGBVC4424, 44" by 24".

d. DSGBVC3654, 36" by 54".

e. DSGBVC4254, 42" by 54".

7. Vertical and horizontal safety support (reversible)

a. DSGBVVH, 30" vertical extension by 34" by 34"

horizontal corner rail.

8. "L" Shaped support (left and right options)

a. DSGBVL1224R, 24" vertical extension by 12" horizontal

- Right.

b. DSGBVL1224L, 24" vertical extension by 12" horizontal

- Left.

c. DSGBVL1836R, 36" vertical extension by 18" horizontal

- Right.

d. DSGBVL1836L, 36" vertical extension by 18" horizontal

- Left.

9. Side support rails (options)

a. DSGBFDRSSW, 33-1/2" Folding & Rotating Safety

Support w/Wallplate

b. DSGBFDSSS, 33-1/2" Folding Safety Support

w/Wallplate

c. DSGBTPH, Toilet Paper Roll Holder

### PART 3 EXECUTION

#### 3.1 EXAMINATION

A. Do not begin installation until substrates finishing operations are completed, including painting.

B. Verify that prepared openings are sized and located in accordance with architects recommendations. Verify that blocking, reinforcement and anchoring devices are the correct type.